

Cropping User's Manual

Version 1.0


ViewCast Corporation

Osprey Video Division

<u>1.</u>	<u>CROPPING: WHAT IS IT AND WHY WOULD ONE USE IT?</u>	<u>4</u>
<u>2.</u>	<u>CROPPING AND THE ROI SETUP</u>	<u>6</u>
<u>3.</u>	<u>CROPPING AND SCALING.....</u>	<u>7</u>
<u>4.</u>	<u>SPECIFYING CROPPING USING THE VIDEO FORMAT DIALOG BOX</u>	<u>9</u>
<u>5.</u>	<u>SPECIFYING CROPPING USING THE CROPPING APPLICATION.....</u>	<u>11</u>
<u>6.</u>	<u>SPECIFYING CROPPING USING THE SDK.....</u>	<u>13</u>
<u>7.</u>	<u>CROPPING LIMITATIONS</u>	<u>14</u>
<u>8.</u>	<u>USING HARDWARE CROPPING WITH WINDOWS MEDIA TOOLS.....</u>	<u>16</u>

1. Cropping: What is it and why would one use it?

Cropping is a method for specifying a region of interest within a video source and discarding video data outside of this region. A typical use of cropping is capturing video that is in a letterbox format. Letterbox material usually contains what appear to be black bars at the top and bottom of the video content.



In the above illustration, the video source that would normally be captured is 640x480 in size. However, the video material of interest is letterboxed and is actually 640x360 in size. The notion of cropping is to crop out the black bars such that only 640x360 is captured.

Why would one want to do this? In the case of letterbox material the answer is fairly simple. By removing unwanted material from what is captured, the amount of captured data is significantly less. If saving to disk, this means

- **Less disk space** is required for saving the material of interest.
- The **throughput**, both on capture and saving to disk, **is smaller** and thus capture is **less demanding** on the host machine.

If encoding the material, either live or the previously saved AVI file:

Cropping Manual
Copyright © ViewCast Corporation, 2001

- The amount of **CPU processing** to encode the video **is less** because there is less data to encode.

Finally, because there is less data to encode:


- More valuable encoding bits can be applied to the material of interest, and thus **quality improves**.

Other reasons for cropping include the removal of noise that is sometimes found on the horizontal or vertical edges of video content. Or maybe one is just interested in a particular area of what a camera is pointing at. Or finally, maybe one needs to have an unscaled image of a size less than that of a full resolution image. In this latter case, without cropping the only way to capture, say a 256x256 sized image, would have been to scale the full resolution image down to this size. With cropping one can capture a 256x256 sized video stream without scaling.

2. Cropping and the ROI setup

Cropping is setup by specifying a rectangular *region of interest (ROI)*. The ROI is composed of:

1. The horizontal offset (X)
2. The vertical offset (Y)
3. The width of the region of interest
4. The height of the region of interest



The offsets for the ROI are the coordinates for the upper-left corner of the ROI within the full-resolution sized image. The example above specifies an ROI of 640x360. The upper-left corner has a horizontal offset of **0** and a vertical offset of **55**. The width of the ROI is **640**. The height of the ROI is **360**. Thus the ROI is said to have an offset of (0,55) and a size of (640,360). When cropping has been setup and enabled, the resultant video, if not further scaled, will be 640x360 in size and, in this example, will not contain black bars at the top and bottom of the image.

3. Cropping and Scaling

On the Osprey cards, cropping is performed in hardware **before** scaling. This is why the setup of cropping is always applied to a full resolution base size. The base size depends on whether video has been configured for a CCIR601 resolution or a Standard/Square-Pixel resolution. Refer to the Osprey User's manual for details on these two resolutions and how they are selected.



In the example used thus far an ROI of (0,55)/(640,360) has been setup based on a square pixel resolution. When cropping is enabled, the ROI size becomes the base size for video capture. Scaling may only be performed to reduce the image size so trying to capture video sizes larger than the ROI size will fail.

In the NTSC space, the size 640x480 is generally accepted to be full resolution at square aspect ratio. It follows that the size 320x240 is also well known and used as well. The 320x240 size represents a horizontal and vertical downscale of 2. Most video hardware, when asked for a 240 or less sized height, usually provides a single field to the application instead of truly scaling down from the full resolution source (480 in height) because this would introduce unwanted interlacing artifacts.

This same notion can be applied to scaling a cropped area. The cropped area, or ROI, is based upon a full resolution area. So if you have been capturing 320x240-sized video, then in this example, you would want to capture a size of 320x180. This represents a scale down of 2 of the ROI in the vertical and horizontal direction.


Cropping Manual
Copyright © ViewCast Corporation, 2001

Warning: if you capture at a size of 320x240 with an ROI of 640x360, you will not maintain the correct aspect ratio! Objects in this case will appear stretched in the vertical direction. The below two pictures represent an ROI of 640x360 that was scaled to 320x240 (the left image) and 320x180 (the right image). Note how the left image appears stretched vertically.



4. Specifying cropping using the video format dialog box

There are three ways to specify the ROI. The first is by using the Format tab in the Osprey Video Format dialog box. The format tab is shown below.



The cropping parameters have been added to the bottom of the tab. The **Enable** check box enables cropping. When not enabled, *one can consider* the ROI to have a vertical and horizontal offset of 0 and to have a width and height equal to the full resolution size. This size is determined by the video format (NTSC/PAL) and by the aspect ratio setting (the Proportion box shown above). In this example, the video format is NTSC and the aspect ratio is selected as standard (i.e. square pixels). Thus the **Source** column in the cropping parameter section on this tab shows the source

Cropping Manual

Copyright © ViewCast Corporation, 2001

width to be 640 and the height to be 480. Recall that the cropping region / ROI is based upon the unscaled full resolution source size.


The four parameters that define the ROI are entered on this tab (width, height, horizontal offset and vertical offset). These values only take effect when cropping is enabled.

Note that in the **Video Size** section the read only entry *Full* indicates a size next to it. This size represents what is considered the full, **unscaled** resolution. In this example, if cropping were not enabled, the full size would be 640x480. However, since the enable check box for cropping has been checked, the full size is now the size of the cropped region / ROI (640x360).

If you select the $\frac{1}{2}$ resolution for the video size, the capture size will be, in this example, 320x180. The $\frac{1}{4}$ size results in a capture size of 160x90. To select a custom scale size, select **custom** in the video size section and then enter a width and height in the custom size section. If you want to maintain the aspect ratio when setting a custom size, select the lock aspect ratio box in the custom size section. This will cause the width and height in this section to maintain a fixed ratio as compared to what is considered the full resolution size.

5. Specifying cropping using the cropping application

The second method for setting cropping is the easiest since it involves using a visual tool to set the ROI.



Above is a snapshot of the cropping application. The **Reference Image** section on the bottom left is read-only and specifies the base full resolution source size. This size is determined by the video format (NTSC/PAL) and by the aspect ratio. In this example, the video format is NTSC and the aspect ratio is selected as square. Thus the reference image has a width of 640 and a height of 480. Recall that the cropping region / ROI is based upon the unscaled full resolution source size. To change the video format, aspect ratio or input port (i.e. composite, svideo, etc) bring-up the video driver format dialog by pressing that button on the right hand side of the crop app.

The crop application shows a live, full resolution preview of the selected video port. Notice the outline of a rectangle overlaid in this video. This is the ROI rectangle. With a mouse a user can move the rectangle around by dragging at the center of the rectangle. The user can also stretch (in or


Cropping Manual

Copyright © ViewCast Corporation, 2001

out) the four sides by pointing and dragging the edges. Or the user can also use the entries (textual and arrow buttons) in the **Cropping Parameters** section to set or fine-tune the ROI parameters.

Once the ROI values are set, the **Set** button saves these values for the corresponding device / board. The **Enable** button actually enables cropping. When this button is pressed its name is changed to **Disable** and video now previewed live is the full resolution ROI.

Please note that there are hardware limitations on the size and offset of the ROI based on the color format of the image being captured. For example, if the color format is RGB16, the offsets and the width and height must be even values. Any cropping values that do not meet the hardware limitations will be rounded down to the closest legal value when you select the **Set** or **Enable** buttons. See the section later in this document on cropping limitations.



6. Specifying cropping using the SDK

The last method for setting the ROI for cropping is using the SDK. For this you must refer to the SDK documentation.

7. Cropping limitations

The following are limitations on how cropping may be used:

- The sum of the width and offset in either direction may not exceed the original base video full-resolution size. For most of the examples above, the base size has been 640x480. Thus one cannot set an ROI of width 640 and a horizontal offset greater than 0. If you attempt to give values that exceed the original image size, the offset will be reduced to the difference between the original image size and the ROI size.
- The scaled image size may not exceed the ROI. Remember, once the ROI has been set and is enabled, the ROI size **becomes** the full / maximum resolution that can be captured. If you attempt to specify a scaled image size greater than the ROI, the scaled image size will be modified to be the same of the ROI. If the Lock Ratio button is checked, the scaled image size will be modified to be the largest possible image size that fits within the ROI and preserves the aspect ratio.
- Be aware that changing the Proportions setting between CCIR601 and Square will affect the original image size. Because of the limitations above, this may result in a change of the cropping values. For example, start with CCIR601 and a ROI of (600,400) at offset (60,40). If you change to square pixels, the ROI violates the first restriction above. As a result, the ROI offset will be automatically changed to (40,40).
- There are hardware limitations on values that can be used for the cropping parameters. The limitations are based on the color format being captured. For example, when capturing RGB16 format, the offsets and the width and height must be even numbers. The table below lists the limitations for various color formats. Any illegal cropping parameters will be rounded down to the closest legal value.

Cropping Manual
Copyright © ViewCast Corporation, 2001

Color Format	Horizontal	Vertical
RGB32	none	even
RGB24	multiple of 4	even
RGB16,RGB15	even	even
RGB8,GRAY8	multiple of 4	even
YUY2 (4:2:2 packed)	even	even
I420 (YUV12 planar)	multiple of 16	even
YVU9 (YVU9 planar)	multiple of 16	multiple of 4

8. Using hardware cropping with Windows Media Tools

The key to using the hardware cropping capabilities today with the Windows Media encoding tools is to keep in mind that:

- Windows Media tools **request a *specific size*** from video capture devices

Part of the process of starting a Windows Media encoding session is selecting a profile that defines the encoding parameters. One set of these parameters happens to be the size of the video to encode. A simple procedure to follow for encoding using hardware cropping is to:

- 1) **Setup the ROI** and note the final **Width** and **Height**
- 2) **Create a new** Windows Media Encoding **Profile** by **copying** one that closely matches the general desired bitrate and resolution **but change the width and height** to the appropriate scaled width and height based on the info from 1.

For example, the *Video for broadband NTSC (384 Kbps Total)* is setup to use video at 320x240. The letterbox example used earlier has an ROI of 640x360. In this case one would go through the process of managing/editing profiles in the Windows Media Encoder application to **copy** the “*Video for broadband NTSC (384 Kbps Total)*” profile. The new copy could be called “*Video for broadband NTSC (384 Kbps Total at 320x180)*”. Once copied and named the profile needs to be edited and the video size set to 320x180. That’s it. When the session is now started the Windows Media Encoding application will request a video size of 320x180 from the Osprey card. Since an ROI has been set and enabled (at 640x360), the Osprey will hardware crop the incoming video (assumed here to be NTSC at a square aspect ratio = 640x480) to 640x360 at the horizontal and vertical offsets setup for the ROI and will scale this ROI down $\frac{1}{2}$ to 320x180. (*Actually, the Osprey drivers will scale horizontally by $\frac{1}{2}$ to get 320 in width but will only return a single field to yield 180 vertical lines. It does this instead of scaling the 360 vertical lines down to 180 because that would introduce interlace artifacts*).

The same notion can be applied to the *Video for broadband NTSC (1500 Kbps Total)* profile. This profile normally encodes 640x480. But why do that with letterbox content? Using the hardware cropping to setup an ROI, for example, of 640x360 and then copying the standard profile and

Cropping Manual
Copyright © ViewCast Corporation, 2001

changing the new one's resolution from 640x480 to 640x360 will result in a significantly improved encoded result.

Encoding from an AVI file: If you set and enable an ROI and capture to an AVI file, when you go to encode from this AVI file you will still have to set up a custom profile as described above. Otherwise, the encoder will scale the video in the AVI file to the size specified in the profile.